





**HEADER (FOR PRINTED CIRCUIT
BOARDS) STRAIGHT SOLDER PIN,
1X1 MM / 0.039X 0.039 IN PIN
SPACING 5,08 mm / 0.2 in
231-332/108-000 TO 231-346/108-000**

PDF DATASHEET

© 1992 - 2011 | CADENAS GmbH

| | |
|---|--|
| ITEM-NO. (ITEM-NO.) | 231-344/108-000 |
| Measured voltage (Measured voltage / V) | 320 |
| Measured shock voltage (Measured shock voltage / kV) | 4 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 12 |
| RM (PIN SPACING / mm) | 5.08 |
| P (NO. OF POLES) | 14 |
| Height (Height / mm) | 12 |
| Width (Width / mm) | 81.02 |
| Depth (Depth / mm) | 8.4 |
| COLOR (COLOR) | orange |
| WEIGHT (WEIGHT / g) | |
| Comment (Comment) | L1 = (No. of poles x Pin Spacing) + 5,9 mm L2 = (No. of poles x Pin Spacing) + 9,9 mm |
| Dimensions (Dimensions) | 1,4 + 0,1 mm |