



**HEADER (FOR PRINTED CIRCUIT
BOARDS) STRAIGHT SOLDER PIN,
1X1 MM / 0.039X 0.039 IN PIN
SPACING 5,08 mm / 0.2 in
231-332/001-000 TO 231-354/001-000**

ITEM-NO. (ITEM-NO.)	231-350/001-000
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5.08
P (NO. OF POLES)	20
Height (Height / mm)	12
Width (Width / mm)	104.8
Depth (Depth / mm)	8.4
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	6.51
Comment (Comment)	A = (No. of poles x Pin Spacing) + 3,2 mm
Dimensions (Dimensions)	1,4 + 0,1 mm