





**HEADER STRAIGHT SOLDER PIN, 1.2  
X 1.2 MM /0.047 X 0.047 IN PIN  
SPACING 5,08 mm / 0.2 in  
231-362/001-000 TO 231-384/001-000**

**PDF DATASHEET**

© 1992 - 2011 CADENAS GmbH

<b>ITEM-NO. (ITEM-NO.)</b>	231-371/001-000
<b>Measured voltage (Measured voltage / V)</b>	320
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	16
<b>RM (PIN SPACING / mm)</b>	5.08
<b>P (NO. OF POLES)</b>	11
<b>Height (Height / mm)</b>	12
<b>Width (Width / mm)</b>	59.08
<b>Depth (Depth / mm)</b>	8.4
<b>COLOR (COLOR)</b>	orange
<b>WEIGHT (WEIGHT / g)</b>	4.31
<b>Comment (Comment)</b>	A = (No. of poles x Pin Spacing) + 3,2 mm
<b>Dimensions (Dimensions)</b>	1,7 + 0,1 mm