





**HEADER STRAIGHT SOLDER PIN, 1.2
X 1.2 MM /0.047 X 0.047 IN PIN
SPACING 5,08 mm / 0.2 in
231-362/001-000 TO 231-384/001-000**

PDF DATASHEET

© 1992 - 2011 CADENAS GmbH

| | |
|---|---|
| ITEM-NO. (ITEM-NO.) | 231-376/001-000 |
| Measured voltage (Measured voltage / V) | 320 |
| Measured shock voltage (Measured shock voltage / kV) | 4 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 16 |
| RM (PIN SPACING / mm) | 5.08 |
| P (NO. OF POLES) | 16 |
| Height (Height / mm) | 12 |
| Width (Width / mm) | 84.48 |
| Depth (Depth / mm) | 8.4 |
| COLOR (COLOR) | orange |
| WEIGHT (WEIGHT / g) | 6.22 |
| Comment (Comment) | A = (No. of poles x Pin Spacing) + 3,2 mm |
| Dimensions (Dimensions) | 1,7 + 0,1 mm |