





**HEADER STRAIGHT SOLDER PIN, 1.2  
X 1.2 MM /0.047 X 0.047 IN PIN  
SPACING 5,08 mm / 0.2 in  
231-362/001-000 TO 231-384/001-000**

|   |   |
|---|---|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 231-378/001-000                           |
| <b>Measured voltage (Measured voltage / V)</b>              | 320                                       |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 4   |
| <b>Pollution degree (Pollution degree)</b>                  | 2   |
| <b>Current intensity (Current intensity / A)</b>            | 16  |
| <b>RM (PIN SPACING / mm)</b>                                | 5.08                                      |
| <b>P (NO. OF POLES)</b>                                     | 18  |
| <b>Height (Height / mm)</b>                                 | 12  |
| <b>Width (Width / mm)</b>                                   | 94.64                                     |
| <b>Depth (Depth / mm)</b>                                   | 8.4                                       |
| <b>COLOR (COLOR)</b>  | orange                                    |
| <b>WEIGHT (WEIGHT / g)</b>                                  | 7.064                                     |
| <b>Comment (Comment)</b>                                    | A = (No. of poles x Pin Spacing) + 3,2 mm |
| <b>Dimensions (Dimensions)</b>                              | 1,7 + 0,1 mm                              |