



**HEADER (FOR PRINTED CIRCUIT
BOARDS) RIGHT ANGLE SOLDER
PIN, 1 X 1 MM / 0.039 X 0.039 IN PIN
SPACING 5 MM / 0.197 IN
231-432/001-000 TO 231-454/001-000**

| | |
|---|--|
| ITEM-NO. (ITEM-NO.) | 231-447/001-000 |
| Measured voltage (Measured voltage / V) | 320 |
| Measured shock voltage (Measured shock voltage / kV) | 4 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 12 |
| RM (PIN SPACING / mm) | 5 |
| P (NO. OF POLES) | 17 |
| Height (Height / mm) | 8.4 |
| Width (Width / mm) | 88.2 |
| Depth (Depth / mm) | 12 |
| COLOR (COLOR) | grau |
| WEIGHT (WEIGHT / g) | 5.648 |
| Comment (Comment) | A = (No. of poles x Pin Spacing) + 3,2 mm B = A + 4,8 mm C = B + 7,2 mm |
| Dimensions (Dimensions) | 1,4 + 0,1 mm |