



**HEADER RIGHT ANGLE SOLDER PIN,
1.2 X 1.2 MM/ 0.047 X 0.047 IN PIN
SPACING 5 MM / 0.197 IN Reflow-
technique**

231-462/001-000/105-604 TO 231-472/
001-000/105-604

ITEM-NO. (ITEM-NO.)	231-463/001-000/105-604
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	3
Height (Height / mm)	8.4
Width (Width / mm)	18.2
Depth (Depth / mm)	12
COLOR (COLOR)	schwarz
Comment (Comment)	L = (No. of poles x Pin Spacing) + 3,2 mm
Dimensions (Dimensions)	1,7 +0,1 mm