






**HEADER RIGHT ANGLE SOLDER PIN,
1.2 X 1.2 MM/ 0.047 X 0.047 IN PIN
SPACING 5 MM / 0.197 IN
231-462/001-000 TO 231-484/001-000**

PDF DATASHEET

© 1992 - 2011 CADENAS GmbH

ITEM-NO. (ITEM-NO.)	231-468/001-000
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	8
Height (Height / mm)	8.4
Width (Width / mm)	43.2
Depth (Depth / mm)	12
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	3.164
Comment (Comment)	A = (No. of poles x Pin Spacing) + 3,2 mm B = A + 4,8 mm C = B + 7,2 mm
Dimensions (Dimensions)	1,7 + 0,1 mm
RGB (RGB)	0.67,0.67,0.67,0