



<b>ITEM-NO. (ITEM-NO.)</b>	231-479/001-000
<b>Measured voltage (Measured voltage / V)</b>	320
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	16
<b>RM (PIN SPACING / mm)</b>	5
<b>P (NO. OF POLES)</b>	19
<b>Height (Height / mm)</b>	8.4
<b>Width (Width / mm)</b>	98.2
<b>Depth (Depth / mm)</b>	12
<b>COLOR (COLOR)</b>	grau
<b>WEIGHT (WEIGHT / g)</b>	7.452
<b>Comment (Comment)</b>	A = (No. of poles x Pin Spacing) + 3,2 mm   B = A + 4,8 mm   C = B + 7,2 mm
<b>Dimensions (Dimensions)</b>	1,7 + 0,1 mm
<b>RGB (RGB)</b>	0.67,0.67,0.67,0