



**HEADER (FOR PRINTED CIRCUIT  
BOARDS) RIGHT ANGLE SOLDER  
PIN, 1 X 1 MM / 0.039 X 0.039 IN PIN  
SPACING 5,08 mm / 0.2 in  
231-532/108/000 TO 231-546/108-000**

<b>ITEM-NO. (ITEM-NO.)</b>	231-539/108-000
<b>Measured voltage (Measured voltage / V)</b>	320
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	12
<b>RM (PIN SPACING / mm)</b>	5.08
<b>P (NO. OF POLES)</b>	9
<b>Height (Height / mm)</b>	8.4
<b>Width (Width / mm)</b>	55.62
<b>Depth (Depth / mm)</b>	12
<b>COLOR (COLOR)</b>	orange
<b>WEIGHT (WEIGHT / g)</b>	3.776
<b>Comment (Comment)</b>	L1 = (No. of poles x Pin Spacing) + 5,9 mm   L2 = (No. of poles x Pin Spacing) + 9,9 mm
<b>Dimensions (Dimensions)</b>	1,4 + 0,1 mm