





**2-CONDUCTOR SPRING CLAMPS PIN
SPACING 5 MM / 0.197 IN 100%
PROTECTED AGAINST MISMATING
231-532/001/000 TO 231-554/001-000**

PDF DATASHEET

© 1992 - 2011 | CADENAS GmbH

ITEM-NO. (ITEM-NO.)	231-540/001-000
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5.08
P (NO. OF POLES)	10
Height (Height / mm)	8.4
Width (Width / mm)	54
Depth (Depth / mm)	12
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	3.39
Comment (Comment)	A = (No. of poles x Pin Spacing) + 3,2 mm B = A + 5,08 mm C = B + 7,4 mm
Dimensions (Dimensions)	1,4 + 0,1 mm