



**HEADER (FOR PRINTED CIRCUIT
BOARDS) RIGHT ANGLE SOLDER
PIN, 1 X 1 MM / 0.039 X 0.039 IN PIN
SPACING 5,08 mm / 0.2 in
231-532/108/000 TO 231-546/108-000**

| | |
|---|--|
| ITEM-NO. (ITEM-NO.) | 231-540/108-000 |
| Measured voltage (Measured voltage / V) | 320 |
| Measured shock voltage (Measured shock voltage / kV) | 4 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 12 |
| RM (PIN SPACING / mm) | 5.08 |
| P (NO. OF POLES) | 10 |
| Height (Height / mm) | 8.4 |
| Width (Width / mm) | 60.7 |
| Depth (Depth / mm) | 12 |
| COLOR (COLOR) | orange |
| WEIGHT (WEIGHT / g) | 4.1 |
| Comment (Comment) | L1 = (No. of poles x Pin Spacing) + 5,9 mm L2 = (No. of poles x Pin Spacing) + 9,9 mm |
| Dimensions (Dimensions) | 1,4 + 0,1 mm |