



**HEADER (FOR PRINTED CIRCUIT
BOARDS) RIGHT ANGLE SOLDER
PIN, 1 X 1 MM / 0.039 X 0.039 IN PIN
SPACING 5,08 mm / 0.2 in
231-532/108/000 TO 231-546/108-000**

ITEM-NO. (ITEM-NO.)	231-545/108-000
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5.08
P (NO. OF POLES)	15
Height (Height / mm)	8.4
Width (Width / mm)	86.1
Depth (Depth / mm)	12
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	
Comment (Comment)	L1 = (No. of poles x Pin Spacing) + 5,9 mm L2 = (No. of poles x Pin Spacing) + 9,9 mm
Dimensions (Dimensions)	1,4 + 0,1 mm