



**1-CONDUCTOR-FEEDTHROUGH
TERMINAL BLOCK RIGHT ANGLE
CONNECTION PIN 1x1.2 MM WITH
FIXING FLANGES FOR
FEEDTHROUGHAPPLICATIONS PIN
SPACING 5 MM / 0.197 IN
231-602/017-000 TO 231-612/017-000**

ITEM-NO. (ITEM-NO.)	231-609/017-000
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 14
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	9
Height (Height / mm)	14.3
Width (Width / mm)	60.2
Depth (Depth / mm)	19.1
No. of connection Points (No. of connection Points)	9
No. of potentials (No. of potentials)	9
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	12.8
Comment (Comment)	L = (No. of poles x Pin Spacing) + 3 mm L1 = L + 5,8 mm L2 = L1 + 6,4 mm
Dimensions (Dimensions)	1,8 + 0,1 mm