





**HEADER (FOR PRINTED CIRCUIT
BOARDS) STRAIGHT SOLDER PIN,
1X1 MM / 0.039X 0.039 IN PIN
SPACING 7,62 mm / 0.3 in
231-732/001-000 TO 231-742/001-000**

PDF DATASHEET

© 1992 - 2011 | CADENAS GmbH

| | |
|---|---|
| ITEM-NO. (ITEM-NO.) | 231-736/001-000 |
| Measured voltage (Measured voltage / V) | 630 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 12 |
| RM (PIN SPACING / mm) | 7.62 |
| P (NO. OF POLES) | 6 |
| Height (Height / mm) | 12 |
| Width (Width / mm) | 46.1 |
| Depth (Depth / mm) | 8.4 |
| COLOR (COLOR) | orange |
| WEIGHT (WEIGHT / g) | 2.43 |
| Comment (Comment) | L = (No. of poles - 1) x Pin Spacing + 8,2 mm |
| Dimensions (Dimensions) | 1,4 + 0,1 mm |