





**HEADER STRAIGHT SOLDER PIN, 1.2
X 1.2 MM /0.047 X 0.047 IN PIN
SPACING 7,62 mm / 0.3 in
231-762/001-000 TO 231-772/001-000**

PDF DATASHEET

© 1992 - 2011 CADENAS GmbH

ITEM-NO. (ITEM-NO.)	231-768/001-000
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	7.62
P (NO. OF POLES)	8
Height (Height / mm)	12
Width (Width / mm)	61.34
Depth (Depth / mm)	8.4
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	3.72
Comment (Comment)	L = (No. of poles - 1) x Pin Spacing + 8,2 mm
Dimensions (Dimensions)	1,7 + 0,1 mm