





**HEADER RIGHT ANGLE SOLDER PIN,
1 X 1 MM / 0.039 X 0.039 IN PIN
SPACING 7.5 MM / 0.295 IN Reflow-
Technique**

231-832/001-000/105-604 TO 231-842/
001-000/105-604

ITEM-NO. (ITEM-NO.)	231-839/001-000/105-604
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	7.5
P (NO. OF POLES)	9
Height (Height / mm)	8.4
Width (Width / mm)	68.2
Depth (Depth / mm)	12
COLOR (COLOR)	schwarz
Comment (Comment)	L = (No. of poles x Pin Spacing) + 8,2 mm
Dimensions (Dimensions)	1,4 +0,1 mm