



| | |
|---|--|
| ITEM-NO. (ITEM-NO.) | 231-841/001-000 |
| Measured voltage (Measured voltage / V) | 630 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 12 |
| RM (PIN SPACING / mm) | 7.5 |
| P (NO. OF POLES) | 11 |
| Height (Height / mm) | 8.4 |
| Width (Width / mm) | 83 |
| Depth (Depth / mm) | 12 |
| COLOR (COLOR) | grau |
| WEIGHT (WEIGHT / g) | 4.614 |
| Comment (Comment) | A = (No. of poles - 1) x Pin Spacing + 8 mm B = A + 5 mm C = B + 7,4 mm |
| Dimensions (Dimensions) | 1,4 + 0,1 mm |