



**HEADER RIGHT ANGLE SOLDER PIN,
1.2 X 1.2 MM/ 0.047 X 0.047 IN PIN
SPACING 7.5 MM / 0.295 IN Reflow-
technique**231-862/001-000/105-604 TO 231-872/
001-000/105-604

| | |
|---|---|
| ITEM-NO. (ITEM-NO.) | 231-871/001-000/105-604 |
| Measured voltage (Measured voltage / V) | 630 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 12 |
| RM (PIN SPACING / mm) | 7.5 |
| P (NO. OF POLES) | 11 |
| Height (Height / mm) | 8.4 |
| Width (Width / mm) | 83.2 |
| Depth (Depth / mm) | 12 |
| COLOR (COLOR) | schwarz |
| Comment (Comment) | L = (No. of poles x Pin Spacing) + 8,2 mm |
| Dimensions (Dimensions) | 1,7 +0,1 mm |