



ITEM-NO. (ITEM-NO.)	231-932/001-000
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	7.62
P (NO. OF POLES)	2
Height (Height / mm)	8.4
Width (Width / mm)	15.82
Depth (Depth / mm)	12
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	0.908
Comment (Comment)	A = (No. of poles - 1) x Pin Spacing + 8,2 mm B = A + 5,08 mm C = B + 7,4 mm
Dimensions (Dimensions)	1,4 + 0,1 mm