





**HEADER RIGHT ANGLE SOLDER PIN,  
1.2 X 1.2 MM/ 0.047 X 0.047 IN PIN  
SPACING 7,62 mm / 0.3 in  
231-962/001-000 TO 231-972/001-000**

<b>ITEM-NO. (ITEM-NO.)</b>	231-965/001-000
<b>Measured voltage (Measured voltage / V)</b>	630
<b>Measured shock voltage (Measured shock voltage / kV)</b>	6
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	16
<b>RM (PIN SPACING / mm)</b>	7.62
<b>P (NO. OF POLES)</b>	5
<b>Height (Height / mm)</b>	8.4
<b>Width (Width / mm)</b>	38.48
<b>Depth (Depth / mm)</b>	12
<b>COLOR (COLOR)</b>	orange
<b>WEIGHT (WEIGHT / g)</b>	2.45
<b>Comment (Comment)</b>	A = (No. of poles - 19 x Pin Spacing + 8,2 mm   B = A + 5,08 mm   C = B + 7,4 mm
<b>Dimensions (Dimensions)</b>	1,7 + 0,1 mm