





**HEADER RIGHT ANGLE SOLDER PIN,
1.2 X 1.2 MM/ 0.047 X 0.047 IN PIN
SPACING 7,62 mm / 0.3 in
231-962/001-000 TO 231-972/001-000**

PDF DATASHEET

© 1992 - 2011 | CADENAS GmbH

ITEM-NO. (ITEM-NO.)	231-971/001-000
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	16
RM (PIN SPACING / mm)	7.62
P (NO. OF POLES)	11
Height (Height / mm)	8.4
Width (Width / mm)	84.2
Depth (Depth / mm)	12
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	5.288
Comment (Comment)	A = (No. of poles - 19 x Pin Spacing + 8,2 mm B = A + 5,08 mm C = B + 7,4 mm
Dimensions (Dimensions)	1,7 + 0,1 mm