





**FEMALE PLUG WITH STRAIGHT
LONG CONTACT PINS PIN SPACING 5
MM / 0.197 IN**
232-132/005-000 TO 232-150/005-000

ITEM-NO. (ITEM-NO.)	232-136/005-000
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	6
Height (Height / mm)	18.25
Width (Width / mm)	31.5
Depth (Depth / mm)	11.6
COLOR (COLOR)	grau
Comment (Comment)	L = (No. of poles x Pin Spacing) + 1,5 mm