



ITEM-NO. (ITEM-NO.)	232-154
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	24
Height (Height / mm)	18.25
Width (Width / mm)	121.5
Depth (Depth / mm)	11.6
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	20.55
Comment (Comment)	L = (No. of poles x Pin Spacing) + 1,5 mm
Dimensions (Dimensions)	1,3 +0,1 mm