





**FEMALE PLUG WITH STRAIGHT
SOLDER PIN PIN SPACING 5,08 mm /
0.2 in
232-162 TO 232-184**

ITEM-NO. (ITEM-NO.)	232-180
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5.08
P (NO. OF POLES)	20
Height (Height / mm)	18.25
Width (Width / mm)	103.1
Depth (Depth / mm)	11.6
COLOR (COLOR)	orange
Comment (Comment)	L = (No. of poles x Pin Spacing) + 1,5 mm
Dimensions (Dimensions)	1,3 +0,1 mm