



**FEMALE PLUG WITH RIGHT ANGLED
SOLDER PIN WITH FIXING FLANGES
FOR FEEDTHROUGHAPPLICATIONS
PIN SPACING 5 MM / 0.197 IN
232-233/031-000 TO 232-254/031-000**

ITEM-NO. (ITEM-NO.)	232-232/031-000
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	2
Height (Height / mm)	11.6
Width (Width / mm)	24.8
Depth (Depth / mm)	18.25
COLOR (COLOR)	grau
Comment (Comment)	L = No. of poles x Pin Spacing L1 = L + 3 mm L2 = L + 8.8 mm L3 = L +14.8 mm
Dimensions (Dimensions)	1.3 +0.1 mm