



**FEMALE PLUG WITH RIGHT ANGLED  
SOLDER PIN WITH FIXING FLANGES  
FOR FEEDTHROUGHAPPLICATIONS  
PIN SPACING 5 MM / 0.197 IN  
232-233/031-000 TO 232-254/031-000**

<b>ITEM-NO. (ITEM-NO.)</b>	232-239/031-000
<b>Measured voltage (Measured voltage / V)</b>	320
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	12
<b>RM (PIN SPACING / mm)</b>	5
<b>P (NO. OF POLES)</b>	9
<b>Height (Height / mm)</b>	11.6
<b>Width (Width / mm)</b>	59.8
<b>Depth (Depth / mm)</b>	18.25
<b>COLOR (COLOR)</b>	grau
<b>Comment (Comment)</b>	L = No. of poles x Pin Spacing   L1 = L + 3 mm   L2 = L + 8.8 mm   L3 = L +14.8 mm
<b>Dimensions (Dimensions)</b>	1.3 +0.1 mm