





**FEMALE PLUG WITH RIGHT ANGLED
SOLDER PIN WITH LOCKING LEVER
PIN SPACING 5.08 MM / 0.2 IN
232-262/039-000 TO 232-284/039-000**

ITEM-NO. (ITEM-NO.)	232-264/039-000
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5.08
P (NO. OF POLES)	4
Height (Height / mm)	11.6
Width (Width / mm)	36.12
Depth (Depth / mm)	18.25
COLOR (COLOR)	orange
Comment (Comment)	L = (No. of poles x Pin Spacing)
Dimensions (Dimensions)	1,3 +0,1 mm