



| | |
|---|---|
| ITEM-NO. (ITEM-NO.) | 232-270 |
| Measured voltage (Measured voltage / V) | 320 |
| Measured shock voltage (Measured shock voltage / kV) | 4 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 12 |
| RM (PIN SPACING / mm) | 5.08 |
| P (NO. OF POLES) | 10 |
| Height (Height / mm) | 11.6 |
| Width (Width / mm) | 52.3 |
| Depth (Depth / mm) | 18.25 |
| COLOR (COLOR) | orange |
| Comment (Comment) | L = (No. of poles x Pin Spacing) + 1,5 mm |
| Dimensions (Dimensions) | 1,3 +0,1 mm |