





**FEMALE PLUG WITH RIGHT ANGLED  
SOLDER PIN WITH LOCKING LEVER  
PIN SPACING 5.08 MM / 0.2 IN  
232-262/039-000 TO 232-284/039-000**

<b>ITEM-NO. (ITEM-NO.)</b>	232-272/039-000
<b>Measured voltage (Measured voltage / V)</b>	320
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	12
<b>RM (PIN SPACING / mm)</b>	5.08
<b>P (NO. OF POLES)</b>	12
<b>Height (Height / mm)</b>	11.6
<b>Width (Width / mm)</b>	76.76
<b>Depth (Depth / mm)</b>	18.25
<b>COLOR (COLOR)</b>	orange
<b>Comment (Comment)</b>	L = (No. of poles x Pin Spacing)
<b>Dimensions (Dimensions)</b>	1,3 +0,1 mm