



| | |
|--|---|
| ITEM-NO. (ITEM-NO.) | 232-302/026-000 |
| Cross section1 (Cross section) | 0.08 - 2.5 |
| Cross section2 (Cross section) | 28 - 12 |
| Strip length (Strip length) | 8 - 9 |
| Measured voltage (Measured voltage) | 320 |
| Measured shock voltage (Measured shock voltage) | 4 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity) | 14 |
| RM (PIN SPACING / mm) | 5.08 |
| P (NO. OF POLES) | 2 |
| Height (Height) | 23.9 |
| Width (Width) | 12.56 |
| Depth (Depth) | 22.75 |
| No. of connection Points (No. of connection Points) | 2 |
| No. of potentials (No. of potentials) | 2 |
| COLOR (COLOR) | orange |
| Comment (Comment) | $L = (\text{No. of poles} \times \text{Pin Spacing}) + 1,5 \text{ mm} + 0,9 \text{ mm}$ |
| Dimensions (Dimensions) | |