



ITEM-NO. (ITEM-NO.)	232-323/026-000
Cross section1 (Cross section)	0.08 - 2.5
Cross section2 (Cross section)	28 - 12
Strip length (Strip length)	8 - 9
Measured voltage (Measured voltage)	320
Measured shock voltage (Measured shock voltage)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity)	14
RM (PIN SPACING / mm)	5.08
P (NO. OF POLES)	23
Height (Height)	23.9
Width (Width)	119.24
Depth (Depth)	22.75
No. of connection Points (No. of connection Points)	23
No. of potentials (No. of potentials)	23
COLOR (COLOR)	orange
Comment (Comment)	$L = (\text{No. of poles} \times \text{Pin Spacing}) + 1,5 \text{ mm} + 0,9 \text{ mm}$
Dimensions (Dimensions)	