



ITEM-NO. (ITEM-NO.)	232-411/026-000
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	14
RM (PIN SPACING / mm)	5.08
P (NO. OF POLES)	11
Height (Height / mm)	19.9
Width (Width / mm)	58.28
Depth (Depth / mm)	22.75
No. of connection Points (No. of connection Points)	11
No. of potentials (No. of potentials)	11
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	20.645
Comment (Comment)	L = (No. of poles x Pin Spacing) + 1,5 mm + 0,9 mm