



ITEM-NO. (ITEM-NO.)	232-503/007-000
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	3
Height (Height / mm)	15
Width (Width / mm)	18.2
Depth (Depth / mm)	42.5
COLOR (COLOR)	grau
Comment (Comment)	L = (No. of poles x Pin Spacing) + 3,2 mm