





**DOUBLE PIN HEADERS PIN 1.2x1.2
MM PIN SPACING 5 MM / 0.197 IN
232-507/007-000 TO 232-524/007-000**

PDF DATASHEET

© 1992 - 2011 | CADENAS GmbH

ITEM-NO. (ITEM-NO.)	232-521/007-000
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	21
Height (Height / mm)	15
Width (Width / mm)	108.2
Depth (Depth / mm)	42.5
COLOR (COLOR)	grau
Comment (Comment)	L = (No. of poles x Pin Spacing) + 3,2 mm