





**FEMALE PLUG WITH STRAIGHT  
LONG CONTACT PINS PIN SPACING  
7,5 mm / 0.295 in  
232-732/005-000 TO 232-742/005-000**

<b>ITEM-NO. (ITEM-NO.)</b>	232-736/005-000
<b>Measured voltage (Measured voltage / V)</b>	400
<b>Measured shock voltage (Measured shock voltage / kV)</b>	6
<b>Pollution degree (Pollution degree)</b>	3
<b>Current intensity (Current intensity / A)</b>	12
<b>RM (PIN SPACING / mm)</b>	7.5
<b>P (NO. OF POLES)</b>	6
<b>Height (Height / mm)</b>	18.25
<b>Width (Width / mm)</b>	44
<b>Depth (Depth / mm)</b>	11.6
<b>COLOR (COLOR)</b>	grau
<b>WEIGHT (WEIGHT / g)</b>	7.29
<b>Comment (Comment)</b>	L = (No. of poles x Pin Spacing) + 1,5 mm