



ITEM-NO. (ITEM-NO.)	232-869
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	7.62
P (NO. OF POLES)	9
Height (Height / mm)	11.6
Width (Width / mm)	67.54
Depth (Depth / mm)	18.25
COLOR (COLOR)	orange
Comment (Comment)	L = (No. of poles - 1) x Pin Spacing + 5,08 mm + 1,5 mm
Dimensions (Dimensions)	1,3 +0,1 mm