





**CONNECTOR FOR EIB  
APPLICATIONS PUSH-WIRE®  
CONNECTION  
243-211**

|  |                              |
|--|------------------------------|
| <b>ITEM-NO. (ITEM-NO.)</b>                                 | 243-211                      |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>     | 4 x 0.6 - 0.8 / 4 x 1        |
| <b>Cross section2 (Cross section / AWG)</b>                | 4 x 22 - 20 / 4 x 18         |
| <b>Strip length (Strip length / mm)</b>                    | 5 - 6                        |
| <b>Measured voltage (Measured voltage / V)</b>             | 100                          |
| <b>Current intensity (Current intensity / A)</b>           | 6                            |
| <b>Height (Height / mm)</b>                                | 11.5                         |
| <b>Width (Width / mm)</b>                                  | 10                           |
| <b>Depth (Depth / mm)</b>                                  | 10                           |
| <b>No. of connection Points (No. of connection Points)</b> | 8                            |
| <b>No. of potentials (No. of potentials)</b>               | 2                            |
| <b>COLOR (COLOR)</b>                                       | dunkelgrau und rot verrastet |
| <b>WEIGHT (WEIGHT / g)</b>                                 | 1.6                          |