





**CONNECTOR FOR EIB
APPLICATIONS PUSH-WIRE®
CONNECTION
243-211**

ITEM-NO. (ITEM-NO.)	243-212
Cross section1 (Cross section / mm²)	4 x 0.6 - 0.8 / 4 x 1
Cross section2 (Cross section / AWG)	4 x 22 - 20 / 4 x 18
Strip length (Strip length / mm)	5 - 6
Measured voltage (Measured voltage / V)	100
Current intensity (Current intensity / A)	6
Height (Height / mm)	11.5
Width (Width / mm)	10
Depth (Depth / mm)	10
No. of connection Points (No. of connection Points)	8
No. of potentials (No. of potentials)	2
COLOR (COLOR)	lichtgrau und gelb verrastet
WEIGHT (WEIGHT / g)	1.547