





**FEMALE CONNECTOR COMPLETE
WITH FIXING SCREWS M4 10 POLE
246-131**

ITEM-NO. (ITEM-NO.)	246-131
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 14
Strip length (Strip length / mm)	8 - 10
Measured voltage (Measured voltage / V)	400
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	16
P (NO. OF POLES)	10
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	37.7