

Overview

Product information



DG301-5.0-10050000087

PCB terminal blocks, Rated current: 17.5A, Rated voltage (III/2) 250V, Cross section: 1.5mm², pitch: 5.0mm, connector method: screw connector with wire protection, Color: blue, Contact surface : Tin

Product advantages

- ☒ Universal installation method to ensure a high degree of flexibility in device design
- ☒ Different poles can be combined through the side lock

Product certification



Technical data

Product drawing

3D model

□

Processing notes

Process

Wave soldering/manual soldering

Connection capacity

Conductor cross section solid

0.75~1.5mm²

Conductor cross section flexible

0.75~1.5mm²

AWG

22~14AWG

Strip length

6mm

Electrical parameters UL

Rated voltage (B)

300V

Rated current (B)	15A
-------------------	-----

Electrical parameters IEC

Rated voltage	250V
Rated current	17.5A
Rated voltage(III/2)	250V
Rated surge voltage(III/2)	2KV

Item properties

Connection direction	0°
Type of installation	PCB welding
Pin arrangement	Single row in a straight line
Connection method	Screw connection with wire protection
Screwdriver	Slotted screwdriver
screw thread	M2.5
Pitch	5mm
Number of potentials	3
Pluggable or not	no
Number of rows	1

Material data

Environmental items	Compliant with REACH/RoHS
Contact material	Copper alloy
Contact point metal surface	tin-plated
Insulation Materials	PBT
Insulating material group	IIIb
Flammability rating	UL94V-0

Mechanical tests

Test Specification	UL1059/IEC60998
--------------------	-----------------

Environmental data

Ambient temperature (operation)	-30°C~120°C(depending on derating curve)
---------------------------------	--

Accessories

Accessories

Coding strip	/
--------------	---

Bridge	DG019-5.0
--------	-----------

Marking strip	/
---------------	---

Others	/
--------	---

Tool

Operating tool	/
----------------	---

Screwdriver	0.6x3.5mm, Slotted screwdriver
-------------	--------------------------------

Business data

Order number	10050000087
--------------	-------------

Packing unit	#N/A
--------------	------

Minimum order quantity	30
------------------------	----

Products weight (without packaging)	#N/A
-------------------------------------	------