





**4-conductor double deck terminal
block 8-conductor through terminal
block L**
2002-2408

ITEM-NO. (ITEM-NO.)	2002-2408
Cross section1 (Cross section / mm²)	0.25 - 2.5 (4)
Cross section2 (Cross section / AWG)	22 - 12
Strip length (Strip length / mm)	10 - 12
Measured voltage (Measured voltage / V)	800
Measured shock voltage (Measured shock voltage / kV)	8
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	24
Height (Height / mm)	52
Width (Width / mm)	5.2
Depth (Depth / mm)	105.5
No. of connection Points (No. of connection Points)	8
No. of potentials (No. of potentials)	2
COLOR (COLOR)	grau
Comment (Comment)	L