



**4-CONDUCTOR THROUGH TERMINAL  
BLOCK SUITABLE FOR EX E  
APPLICATIONS CENTRE-/ LATERAL  
MARKING**  
2001-1401

|   |                  |
|---|------------------|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 2001-1404        |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>      | 0.25 - 1.5 (2.5) |
| <b>Cross section2 (Cross section / AWG)</b>                 | 22 - 14          |
| <b>Strip length (Strip length / mm)</b>                     | 9 - 11           |
| <b>Measured voltage (Measured voltage / V)</b>              | 800              |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 8                |
| <b>Pollution degree (Pollution degree)</b>                  | 3                |
| <b>Current intensity (Current intensity / A)</b>            | 18               |
| <b>Height (Height / mm)</b>                                 | 33               |
| <b>Width (Width / mm)</b>                                   | 4.2              |
| <b>Depth (Depth / mm)</b>                                   | 70               |
| <b>No. of connection Points (No. of connection Points)</b>  | 4                |
| <b>No. of potentials (No. of potentials)</b>                | 1                |
| <b>COLOR (COLOR)</b>  | blau             |
| <b>WEIGHT (WEIGHT / g)</b>                                  | 5.887            |