



| | |
|---|----------------|
| ITEM-NO. (ITEM-NO.) | 2000-1201 |
| Cross section1 (Cross section / mm²) | 0.14 - 1 (1.5) |
| Cross section2 (Cross section / AWG) | 24 - 16 |
| Strip length (Strip length / mm) | 9 - 11 |
| Measured voltage (Measured voltage / V) | 800 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 3 |
| Current intensity (Current intensity / A) | 13.5 |
| Height (Height / mm) | 33 |
| Width (Width / mm) | 3.5 |
| Depth (Depth / mm) | 48.5 |
| No. of connection Points (No. of connection Points) | 2 |
| No. of potentials (No. of potentials) | 1 |
| COLOR (COLOR) | grau |
| WEIGHT (WEIGHT / g) | 3.53 |