





**2-Conductor fuse terminal block
for mini-automotive blade-type fuses
with testing facility 12 V
282-698/281-429**

ITEM-NO. (ITEM-NO.)	282-698/281-429
Cross section1 (Cross section / mm²)	0.2 - 6
Cross section2 (Cross section / AWG)	24 - 10
Strip length (Strip length / mm)	12 - 13
Measured voltage (Measured voltage / V)	400
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	25
Height (Height / mm)	33.5
Width (Width / mm)	8
Depth (Depth / mm)	85
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	2
COLOR (COLOR)	grau
Comment (Comment)	Schaltung I