



ITEM-NO. (ITEM-NO.)	2000-1304
Cross section1 (Cross section / mm²)	0.14 - 1 (1.5)
Cross section2 (Cross section / AWG)	24 - 16
Strip length (Strip length / mm)	9 - 11
Measured voltage (Measured voltage / V)	800
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	13.5
Height (Height / mm)	33
Width (Width / mm)	3.5
Depth (Depth / mm)	58.5
No. of connection Points (No. of connection Points)	3
No. of potentials (No. of potentials)	1
COLOR (COLOR)	blau
WEIGHT (WEIGHT / g)	
RGB (RGB)	0.38,0.35,0.95,0