



ITEM-NO. (ITEM-NO.)	285-154
Cross section1 (Cross section / mm²)	10 - 50 (70 "f")
Cross section2 (Cross section / AWG)	8 - 2 / 0
Strip length (Strip length / mm)	30
Measured voltage (Measured voltage / V)	1000
Measured shock voltage (Measured shock voltage / kV)	8
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	150
Height (Height / mm)	87
Width (Width / mm)	20
Depth (Depth / mm)	94
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	1
COLOR (COLOR)	blau
WEIGHT (WEIGHT / g)	157.22
Comment (Comment)	nur auf TS 35 x 15; 2.3 mm dick