




VOLTAGE TAP FOR 95 mm² HIGH CURRENT TERMINAL BLOCKS 285-407

© 1992 - 2011 CADENAS GmbH











VOLTAGE TAP FOR 95 mm² HIGH CURRENT TERMINAL BLOCKS 285-407



© 1992 - 2011 CADENAS GmbH

ITEM-NO. (ITEM-NO.)	285-407
Cross section1 (Cross section / mm²)	0.2 - 10
Cross section2 (Cross section / AWG)	24 - 08
Measured voltage (Measured voltage / V)	1000
Measured shock voltage (Measured shock voltage / kV)	8
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	57
Height (Height / mm)	
Width (Width / mm)	20
Depth (Depth / mm)	
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	2
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	22.5