


Plugs

SLS 200



Product	SLS 200
description	Contact protected plug with screw connection for cables up to 2.5 mm², with onward connection capability (4 mm socket). Insulated by latching and sprung insulating sleeve, to be released by pressure on the lateral locking spring. plug with contact spring, 4mm diameter. *For this typ up to DC 150 V, CAT II according IEC/EN 61010-31 item 6.4., comment 4 allowed for devices with not yet protected sockets.
operating instruction	BA412
article-no. / *colour	9321531xx  00 black  01 red  02 blue  03 yellow  04 green Ni
drawing	
	
technical data	
connection	screw terminal
rated voltage	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽²⁾
rated current (consider derating curve)	30 A
material plug	brass, nickel plated
housing material	PP
temperature range acc. To IEC61010 ⁽¹⁾	-25 °C to +80 °C

4 mm sliding sleeve system

inflammability class acc. to UL 94 (only valid for basic material of housing)	HB
--	----

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges

⁽²⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 21.06.2022

stand: 21.06.2022