



ALL DIMENSION IN MM UNLESS OTHERWISE STATED : 0.= ±0.1mm 00.= ±0.2mm 000.= ±0.3mm

HEAVY POWER CO., LTD <i>A Specialist Manufacturer</i> No.7, Lane 106, Wukung 3rd. Road, Wuku Industrial Park, Taipei Hsien, Taiwan 248 Tel : 886-2-22983178 Fax : 886-2-22983183	Scale :	Date : 2007.05.30	TITLE : EASY-LINK LIGHTING CONNECTORS PART NO. PC302	
	Housing Material : Thermoplastic, UL 94V-2 Voltage : VDE-450V Current : 24A(VDE) Working Temp : 100°C Wire Range : Installation side: 0.75-2.5mm ² .sol Lighting side: 0.5-2.5mm ² .sol/str Stripping Length : 9-11mm /0.39-0.45inch		PREPARED yao	REV. 1.0
DWG NO. PC302	International Approvals CE, VDE, FIMKO, KEMA, CEBEC			